

LSRFortessa Configuration

	Mirror	Filter	Fluorochrome Examples
488 60mW	685LP	710/50	PerCP-Cy5.5
	505LP	530/30	FITC, GFP, AF488
		488/10	SSC

405 100mW	750LP	780/60	BV786
	690LP	710/50	BV711
	635LP	670/14	BV650
	595LP	610/20	BV605
	505LP	525/50	BV510
		450/50	BV421, Pacific Blue

355 100mW	690LP	740/35	BUV737
	450LP	515/30	BUV496
		379/28	BUV395

640 60mW	750LP	780/60	APC-Cy7
	685LP	730/45	AF700
		670/30	APC

561 50mW	750LP	780/60	PE-Cy7
	635LP	670/30	PE-Cy5
	595LP	610/20	PE-Texas Red, AF594, mCherry
		586/15	PE, dTomato, DsRed

Detector
A
B
C

A
B
C
D
E
F

A
B
C

A
B
C

A
B
C
D